


Based on superior E-Pi technology, Thermo Scientific STD5000 and STD6000 current-to-pressure (I/P) transducers set the standard in the industry for reliable electronic input signal conversion. An innovative, field-proven design and superior technology ensure accuracy, reliability and ease-of-use to facilitate operations and increase productivity.

## Thermo Scientific STD5000 & STD6000

### Current-to-Pressure (I/P) Transducers



#### Features and Benefits

- Accuracies of  $\pm 0.15\%$  to  $\pm 0.25\%$  of span
- Advanced E-Pi technology that is unaffected by vibration, shock or mounting position
- High supply pressure ranges of 35 PSIG to 100 PSIG available with select output ranges
- Intrinsically safe or explosion-proof models available
- Operating temperature range of  $-40^{\circ}\text{C}$  to  $+66^{\circ}\text{C}$  ( $-40^{\circ}\text{F}$  to  $+150^{\circ}\text{F}$ )
- Rugged NEMA 4X and IP65 enclosure
- Field-selectable direct and reverse modes

#### Accurate & Reliable

The rugged, compact Thermo Scientific STD5000 and STD6000 current-to-pressure (I/P) transducers provide reliable electronic input signal conversion in the most demanding industrial environments. Backed by our field-proven E-Pi technology, these transducers ensure accurate, repeatable performance that is unaffected by shock, vibration or mounting position, minimizing maintenance and increasing process optimization.

#### Field-Proven & Stable

Field-proven Thermo Scientific E-Pi transducer technology is recognized as a revolutionary breakthrough that provided the industry with its first "solid state" I/P transducer. This advanced E-Pi technology uses a minimal amount of electrical energy and air consumption to convert a 4-20 mA input signal to a proportional pneumatic output signal (3-15 PSIG, 0.2-1 BAR, etc.). This pneumatic (backpressure) output is precisely modulated by a virtually weightless, low mass membrane that is held in a continuously balanced position. The output of the E-Pi is

fed into an integral volume booster to deliver a pneumatic output signal with an output capacity of 4.0 SCFM. Overall performance, accuracy and repeatability are further enhanced via an internal feedback network that allows the transducer to quickly respond to input changes. These balanced supply and exhaust dynamics enhance stability while delivering accuracies of  $\pm 0.15\%$  to  $\pm 0.25\%$  of span for superior process control.

#### Easy to Install & Maintain

When the installation area is limited, the compact size of the transducer enables it to be situated on the valve as needed, including at an angle or upside down, with no effect on functionality. In addition, the rugged NEMA 4X housing ensures durability and long life for maximum return on investment.

## Thermo Scientific STD5000 & STD6000 Current-to-Pressure (I/P) Transducers

### Functional Specifications

Accuracy	±0.15% of span (3-15 and 1-17 PSIG output); ±0.25% of span (3-27 and 6-30 PSIG output)
Repeatability	0.05% of span
Deadband	0.02% of span
Stability/Reproducibility	0.5% of span/6 months
Output Capacity	Standard: 4.0 SCFM (supply and exhaust characteristics are balanced to within ±10%) High Pressure: 4-8 SCFM possible (dependent on air supply and tubing size)
Air Consumption	0.04 SCFM steady state average (0.06 SCFM maximum)
Position Effect	Not measurable
Vibration Effect	<0.25% from 1-200 Hz/1g
Frequency Response	-3 db at 5 Hz (per ISA-S26.4.3.1 Configuration A)
Loop Load	3.8 VDC + 5 ohm (195 ohm load at 20 mA)
Operating Current	3.7 mA min; 200 mA max; continuous at 120°F half cycle 70 amp 1/120 second at 68°F
Supply Pressure	Standard: minimum of 3 PSIG and maximum of 10 PSIG above the maximum calibrated output High Pressure: for outputs of 3-15 PSIG and 0.2 to 1.0 BAR, supply range is 35 to 100 PSIG or 2.4 to 6.9 BAR; Pressures below 35 may affect the output of the unit; Other output ranges may be possible (consult Thermo Fisher Scientific)
Air Supply	Clean, dry and oil-free instrument air
Operating Temperature	-40°C to +66°C (-40°F to +150°F)
Temperature Effect	Range of +18°C to +66°C (0°F to +150°F): ±0.02% / °F of span; Range -40°C to +66°C (-40°F to +150°F): ±0.04% / °F of span
RFI-EMI Effect	Less than ±1% effect on zero/span (26-1000 mHz @ 30V/m) when installed per product installation guidelines
Operational Modes	Field selectable direct, reverse and/or split range; see notes in model number description
Failure Mode	Mechanically direct (i.e., if the input current drops below 3.7 mA DC, the output will drop to 1 to 2 PSIG regardless of direct or reverse mode selection)


### Physical Specifications

Enclosure	Internally purged NEMA 4X/IP65; cast/machined aluminum with powder-coated epoxy
Connections	Supply port: 1/4-in NPTF (1X) Pneumatic Output Port: 1/4-in NPTF (2X) Electrical: 1/2-in NPTF conduit (2X); terminals 12-22 AWG wire
Weight	1.13 kg (2.5 lbs)

### Certifications

ATEX	STD5000: intrinsically safe, 4-20 mA models only; II 1G Ga Ex ia IIC T4 [Tamb -20°C to +60°C (-4°F to +140°F)]; II 1D Da Ex iaD 20 T+62°C (+144°F) STD6000: flameproof; II 2 G Ex d IIC T5 [Tamb -20°C to +50°C (-4°F to +122°F)]; II 2 D Ex td A21 IP6X T+100°C (+212°F)
CSA/US	STD5000: intrinsically safe, 4-20 mA models only; Class I, Div 2, Groups A, B, C & D; Class I, Div 1, Groups A & B; Class II, Div 1, Groups E, F & G; Class III, Div 1 when connected to CSA certified barriers rated 31.5V max, 463 ohms min, T3C; Class I, Div 1, Groups C & D; Class II, Div 1, Groups E, F & G; Class III, Div 1 when connected to CSA certified barriers rated 28V max, 120 ohms min, T3C; STD6000: Class I, Div 2, Groups A, B, C & D; Class I, Div 1, Groups B, C & D; Class II, Div 1, Groups E, F & G; Class III, Div 1
CE	Compliant

### Ordering Information



© 2010 Thermo Fisher Scientific Inc. All rights reserved. Results may vary under different operating conditions. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. Literature Code PI.2063.1210

Unit 702-715, 7/F Tower West Yonghe Plaza No. 28, Andingmen East Street Beijing 100007 CHINA	+86 (10) 8419-3588 +86 (10) 8419-3580 fax
A-101, ICC Trade Tower, Senapati Bapat Road Pune 411016 Maharashtra INDIA	+91 (20) 6626 7000 +91 (20) 6626 7001 fax
Ion Path, Road Three, Winsford, Cheshire CW7 3GA UK	+44 (0) 1606 548700 +44 (0) 1606 548711 fax
1410 Gillingham Lane Sugar Land, TX 77478 USA	+1 (800) 437-7979 +1 (713) 272-0404 +1 (713) 272-4573 fax