

Silicone Rubber Griffin Beaker Heaters

Product Highlights

- ✓ Provides Even Heat for Griffin and Standard Beaker Heating Applications.
- ✓ Removable with hook and loop fastener. Easy-Access to Graduation.
- ✓ Moisture and Chemical Resistant. No Need to Worry About Spills.



Specifications:

- Maximum exposure temperature: 232°C (450°F)
- 120 or 240VAC
- Power density: 5.0 watts/in² (0.008 watts/mm²)
- Heating element is laminated between two layers of 15mil fiberglass reinforced silicone rubber
- 1" (25mm) wide hook and loop fastener
- Moisture, chemical, and radiation resistant
- Dielectric strength of over 2000 volts
- 24" (610mm) long power leads with
 - 120VAC: Standard 2-prong NEMA 1-15 plug
 - 240VAC: Crimped wire ferrule terminated leads



Ordering Information:

Size ml	Diameter in (mm)	Heater Height in (mm)	Heater Length in (mm)	Total Watts	Part Number 120VAC	Part Number 240VAC
250	2.7 (69)	3.0 (76)	12.25 (311)	150	GBH0250-1	GBH0250-2
400	3.0 (76)	3.5 (89)	13.75 (349)	200	GBH0400-1	GBH0400-2
600	3.6 (91)	4.0 (102)	15.00 (381)	250	GBH0600-1	GBH0600-2
1000	4.3 (109)	4.6 (117)	17.25 (438)	350	GBH1000-1	GBH1000-2

IMPORTANT: Temperature controller is required for this product. See **pages 86 through 104** for options.

BriskHeat® offers a wide variety of temperature control options including the SDC Benchtop Digital Temperature Controller.



Need a different size or have a different object to heat? We can design a heater specifically for your application. **Contact us or your local distributor for more details.**