

CHEMO PREP MAT / SPILL PADS

NON-STERILE






Technical Data Sheet

Description

Our Chemo Prep Mats are designed for use in your cleanroom, barrier isolator, or glove box during HD compounding. These mats will quickly and safely remove spills before they spread.

Features and Benefits

- Absorbent, 3 ply material
- Non-Sterile
- Non-porous backing
- Ideal for ISO class 5 cleanrooms and higher
- Made in the USA



Performance Characteristics:

Test	Value
Basic Weight	152 gsm
Thickness	0.68 mm
Total Absorbency <i>Total absorbency percentage is the weight of the water divided by the sample weight</i>	790% (12.25 g/ 1.55g)
Absorbency Capacity (IEST-RP-CC004.4)	650 mL/m ²
Particle Counts (IEST-RP-CC004.4)	93.47 x 10 ⁶
Elemendorf Tear	
MD	377g
TD	160g
Tensile Yield	
MD	6.44 lbs
TD	6.03 lbs
Tensile Break	
MD	3.61 lbs
TD	4.81 lbs
Tensile Break	
MD	745%
TD	155%

Packaging:

SKU #	Size	Color	Description	Packaging
CM-1611.50	16" x 11"	White/Blue	LINT FREE, HIGHLY ABSORBENT, NON-POROUS BACKING	50 PCS/BAG, 4 BAGS/CASE
CM-2216.50	22" x 16"	White/Blue	LINT FREE, HIGHLY ABSORBENT, NON-POROUS BACKING	50 PCS/BAG, 4 BAGS/CASE

The above is typical physical property test data applicable to the sample reference name and should not be construed as a specification.

Disclaimer: The information supplied in this document is for guidance only and should not be construed as a warranty. All implied warranties are expressly disclaimed, including without limitation any warranty of merchantability and fitness for use. All users of the material are responsible for assuring that it is suitable for their needs, environment and end use. All data is subject to change as High-Tech Conversions deems appropriate.

