

CONDUCTIVITY PROBES

027 212 General Purpose Epoxy Bodied Conductivity Probe

- Description**

This probe is designed for standard measurements of general solutions. It is designed for general purpose conductivity measurement for accurate Q.C. and research work.



- Technical specifications**

Parameter	Specification
Cell Constant	$K = 1 \pm 20\%$
Recommended Measurement Range	0 – 10mS/cm
Temperature Range	0-80°C (100°C intermittent)
Temperature Compensation	Thermistor 10 K @ 25°C
Body Material	Epoxy
Plate Material	Carbon
Dimensions	120x12mm
Cable Length	1 metre (nominal)
Termination	7 pin DIN

This electrode is suitable for use with Jenway conductivity meters 4510, 4520 and 3540.

This datasheet is for your guidance only.