



**Precalibrated &  
Ready to Use!**

## Thermohygrometers

**Compact, lightweight design for accurate measurements anywhere!**

Ergonomic handheld thermohygrometers provide a fast and convenient way to accurately spot-check relative humidity and temperature in a wide range of environments and applications. When accuracy is a must in the field, in the lab, or on the process floor, these meters deliver dependable results every time!

### Features

- ◆ Reliable measurements, guaranteed! Precalibrated to NIST-traceable standards.\*
- ◆ Large backlit LCD displays humidity, temperature, dew point, and wet bulb readings
- ◆ Feature Min/Max readings and Hold function
- ◆ User-selectable temperature readout in °C or °F
- ◆ Integrated humidity and thermistor (NTC) temperature sensor
- ◆ Auto power-off mode extends battery life

### Additional features for model 20250-11

- ◆ Absolute humidity measurements

### Additional features for model 20250-12

- ◆ External thermocouple type K input
- ◆ Target superheat mode (TSH) and target evaporator exit temperature (TEET) calculations provide more accurate balancing of airflow systems
- ◆ Dry bulb measurement

### Additional features for model 20250-21

- ◆ Heavy-duty housing protects against knocks and jars
- ◆ Absolute humidity measurements

## Applications

- ◆ HVAC
- ◆ Industrial
- ◆ Food industry
- ◆ Educational
- ◆ Laboratory
- ◆ R&D

\*Calibration certificate provided by InnoCal®, an ISO17025 accredited laboratory (A2LA certificate 1746.01) offering a broad range of NIST-traceable calibration services.

For recalibration, call 866-466-6225 or e-mail [info@innocal.com](mailto:info@innocal.com). Their full complement of services can be viewed at [www.innocal.com](http://www.innocal.com).



Description	Thermohygrometer	Thermohygrometer with single type K input and superheat function	Professional thermohygrometer
Catalog number	MW-20250-11	MW-20250-12	MW-20250-21
<b>Range</b>			
Humidity	0 to 100% RH	0 to 100% RH	0 to 100% RH
Absolute humidity (calculated)	0 to 500 g/m <sup>3</sup> , 0 to 218.5 gr/ft <sup>3</sup> >	—	0 to 500 g/m <sup>3</sup> , 0 to 218.5 gr/ft <sup>3</sup>
Temperature (NTC)	-22 to 212°F (-30 to 100°C)	32 to 140°F (0 to 60°C)	-22 to 212°F (-30 to 100°C)
Temperature (T/C)	—	-328 to 2501°F (-200 to 1372°C)	—
Dew point (calculated)	-22 to 212°F (-30 to 100°C)	-22 to 212°F (-30 to 100°C)	-22 to 212°F (-30 to 100°C)
Wet bulb (calculated)	32 to 176°F (0 to 80°C)	32 to 176°F (0 to 80°C)	32 to 176°F (0 to 80°C)
<b>Resolution</b>			
Humidity	0.1	0.1	0.1
Temperature (NTC)	0.1°F/C	0.1°F/C	0.1°F/C
Temperature (T/C)	—	0.1° (<1000°) or 1° (≥1000°)	—
<b>Accuracy</b>			
Humidity	±2% from 40 to 60% RH; ±3% from 20 to 40% RH and 60 to 80% RH; ±4% from 0 to 20% RH and 80 to 100% RH	±2.5% from 10 to 90% RH; ±5% from 0 to 10% RH and 90 to 100% RH	±2% from 40 to 60% RH; ±3% from 20 to 40% RH and 60 to 80% RH; ±4% from 0 to 20% RH and 80 to 100% RH
Temperature (NTC)	±0.9°F (0.5°C) from -4 to 140°F (-20 to 60°C); ±1.8°F (1°C) from -22 to -4°F (-30 to 19°C) and 140 to 212°F (60 to 100°C)	±1.8°F (1°C)	±1.8°F (1°C) from -4 to 140°F (-20 to 60°C); ±2.7°F (1.5°C) from -22 to -4°F (-30 to 19°C) and 140 to 212°F (60 to 100°C)
Temperature (T/C)	—	±[0.5% reading + 1.8°F (1°C)] above -148°F (-100°C); ±[0.5% reading + 3.6°F (2°C)] below -148°F (-100°C)	—
<b>General</b>			
Dimensions (L x W x H)	6½" x 2½" x 1¾" (16.5 x 5.4 x 3.4 cm)	7¼" x 2½" x 1" (18.5 x 6.3 x 2.6 cm)	11⅞" x 3" x 2" (30 x 7.5 x 5 cm)
Power	Three AAA batteries	Three AAA batteries	One 9 V battery
Accessories included	Carrying case, batteries, NIST-traceable certificate with data and uncertainties	One type K flexible probe, carrying pouch, batteries, NIST-traceable certificate with data and uncertainties	Carrying case, battery, NIST-traceable certificate with data and uncertainties



### USA

#### Cole-Parmer

Toll-free: 800-323-4340  
Phone: 847-549-7600  
[ColeParmer.com](http://ColeParmer.com)

#### Davis Instruments

Toll-free: 800-358-5525  
Phone: 847-327-2000  
[Davis.com](http://Davis.com)

#### For Calibration, InnoCal

Toll-free: 866-466-6225  
[InnoCalSolutions.com](http://InnoCalSolutions.com)

### CANADA

Toll-free: 800-363-5900  
Phone: 514-355-6100  
[ColeParmer.ca](http://ColeParmer.ca)

### UNITED KINGDOM

Free Phone: 0500-345-300  
Phone: 020-8574-7556  
[ColeParmer.co.uk](http://ColeParmer.co.uk)

### INDIA

Phone: 91-22-6716-222  
[ColeParmer.in](http://ColeParmer.in)

### INTERNATIONAL CUSTOMERS

Call 847-549-7600  
[ColeParmer.com/dealers](http://ColeParmer.com/dealers)