



DIGI-SENSE™
THE STANDARD IN PRECISION MEASUREMENT



**Precalibrated &
Ready to Use!**

Hot-Wire Anemometer

High accuracy even at very low air velocities and flow rates

Achieve precise air velocity and airflow measurements with this rugged hot-wire anemometer. Maximize performance for safety and comfort by analyzing and storing measurements for future review. Read air velocity or airflow, and temperature simultaneously on the large LCD, in nine user-selectable units of measurement.

Features

- ◆ Reliable measurements, guaranteed! Precalibrated to NIST-traceable standards.*
- ◆ Slim, telescoping hot-wire probe is ideal for grilles and diffusers
- ◆ User-selectable units of air measurement: ft/min, m/s, mph, km/h, knots, CFM, and CMM
- ◆ Measure air velocities up to 4925 ft/min (25 m/s)
- ◆ Measure airflow up to 99,999 CFM (99,999 CMM)
- ◆ Large, dual-function LCD with backlight for easy reading in low-light conditions
- ◆ Auto power-off extends battery life
- ◆ Download measurements into a PC for analysis and storage with the software and USB cable (included)

Applications

- ◆ Analyze, balance, and troubleshoot ventilation performance in protected storage areas, home, and office environments
- ◆ Evaluate cooling air in high-temperature processing environments
- ◆ Perform environmental testing
- ◆ Measure and validate air conveyors, blowers, motors, furnace exhaust, flow hoods, cleanrooms, and paint spray booths

Includes

Telescoping hot-wire probe sensor with cable, USB cable, software CD, hard carrying case, AC/DC power adapter, one 9 V battery, and NIST-traceable certificate with data and uncertainties.

*Calibration certificate provided by InnoCal®, an ISO17025 accredited laboratory (A2LA certificate 1746.01) offering a broad range of NIST-traceable calibration services. For recalibration, call 866-466-6225 or e-mail info@innocalsolutions.com. Their full complement of services can be viewed at www.innocalsolutions.com.

Specifications

Parameters	Range	Resolution	Accuracy
Air velocity			
Feet per minute (ft/min)	20 to 4925	1	±(5% + 1 digit) reading or ±(1% + 1 digit) full scale, whichever is greater
Meters per second (m/s)	0.1 to 25.0	0.01	
Miles per hour (mph)	0.2 to 55.8	0.1	
Kilometers per hour (km/h)	0.3 to 90.0	0.1	
Knots	0.2 to 485	0.1	
Airflow			
CFM (cubic feet per min)	0 to 99,999	0.001 to 100	—
CMM (cubic meter per min)	0 to 99,999	0.001 to 100	—
Temperature			
°F	32 to 122	0.1	±1.8
°C	0 to 50	0.1	±1

Functions: measure, max/min/avg, hold reading

Sampling rate: approximately once per 0.8 second

User-selectable units: ft/min, m/s, mph, km/h, knots, CFM, CMM, °F, °C

Dimensions: 8¼" x 3" x 2" (21 x 7.5 x 5 cm)

Memory: maximum and minimum with recall

Power: one 9 V battery

Display: dual-function backlit LCD, 1⅞" x 2⅜" (4.7 x 6 cm)



Catalog number	Description
MW-20250-16	Hot-wire anemometer



USA

Cole-Parmer

Toll-free: 800-323-4340
Phone: 847-549-7600
ColeParmer.com

Davis Instruments

Toll-free: 800-358-5525
Phone: 847-327-2000
Davis.com

For Calibration, InnoCal

Toll-free: 866-466-6225
InnoCalSolutions.com

CANADA

Toll-free: 800-363-5900
Phone: 514-355-6100
ColeParmer.ca

UNITED KINGDOM

Free Phone: 0500-345-300
Phone: 020-8574-7556
ColeParmer.co.uk

INDIA

Phone: 91-22-6716-222
ColeParmer.in

INTERNATIONAL CUSTOMERS

Call 847-549-7600
ColeParmer.com/dealers