

# Excelon® Bev-A-Line® V HT Tubing

Bev-A-Line® V HT Tubing is a lightweight, transparent tubing designed to be flexible across a broad temperature range. Made from high-temperature polyethylene copolymer, this tubing offers enhanced heat resistance compared to standard polyethylene.


This tubing's low friction coefficient and great chemical resistance allow easy transfer of solids, alcohols, acids, caustics, and solvents. The smooth interior surface is exceptionally resistant to the absorption of liquids, providing a neutral and stain-free environment.



## CERTIFICATION

USP Class VI compliant

## EXCELON V HT TUBING



## APPLICATIONS

- Perfect for coffee dispensing and confectionary production
- Ideal for general-purpose, laboratory, and single-use applications

## FEATURES/BENEFITS

- Higher temperature version of Bev-A-Line® IV
- Clear shell provides excellent durability and greater burst strength than PVC
- Wide temperature range of -51 to 82 °C (-60 to 180 °F)
- Flexible tubing with a 75 Shore A durometer
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
France	+33 (0) 1486 37800

Germany	+49 (0) 9377 92030
India	+1.800.266.1244
Italy	+39.02.84349215
UK	+44 (0) 1480.272279
All others	+1.847.549.7600

## Specification and Ordering Table

Brand	Dimensions: in. (mm)			Item number	Reel length (ft)
	Tubing ID	Tubing OD	Wall		
Excelon	1/16" (1.6)	3/16" (4.8)	1/16" (1.6)	<a href="#">50117-61</a>	50
	1/8" (3.2)	3/16" (4.8)	1/32" (0.8)	<a href="#">50117-62</a>	50
	1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	<a href="#">50117-63</a>	50
	3/16" (4.8)	1/4" (6.4)	1/32" (0.8)	<a href="#">50117-64</a>	50
	3/16" (4.8)	5/16" (8)	1/16" (1.6)	<a href="#">50117-65</a>	50
	1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	<a href="#">50117-66</a>	50
	5/16" (8)	7/16" (11)	1/16" (1.6)	<a href="#">50117-67</a>	50
	3/8" (9.5)	1/2" (12.7)	1/16" (1.6)	<a href="#">50117-68</a>	50
	3/4" (19.1)	1" (25.4)	1/8" (3.2)	<a href="#">50117-69</a>	50