

Cole-Parmer® Peroxide-Cured Silicone 3-Stop Pump Tubing


Stopped tubing ensures a perfect fit every time. Stops hold tubing in the pump head for optimal tension, resulting in reliable pumping and repeatable flow rates. Three stops give you two tubing sections instead of just one. When one tubing section wears, a new section is ready to use. The high-performance, peroxide-cured silicone tubing features a smooth bore to inhibit microbial growth and ensure effortless fluid transfer. Enhanced mechanical strength and high elasticity make the tubing ideal for use in peristaltic pumps. Tubing also exhibits a wide operating temperature range, excellent chemical resistance, and kink resistance.



CERTIFICATION

USP Class VI and US Pharmacopoeia compliant

PEROXIDE-CURED SILICONE 3-STOP PUMP TUBING SIZE



APPLICATIONS

- Perfect for laboratory applications and use in peristaltic pumps
- Ideal for general-purpose, laboratory, and single-use applications

FEATURES/BENEFITS

- Three tubing stops are color-coded for easy size identification
- Sterilize via ethylene oxide, gamma irradiation, and autoclave
- Withstands a wide temperature range of -50 to 230 °C (-58 to 446 °F)
- Flexible tubing with a 60 Shore A durometer
- Translucent tubing—perfect for visual flow confirmation
- Tubing does not contain SVHCs as classified by the REACH environmental regulation
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®

coleparmer.com

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

Specification and Ordering Table

Dimensions: mm (in.)			Color-Coded Stops	Tubes/Pack	Item Number
Tubing ID	Length Between Stops	Tubing Length			
0.89 (0.035")	67 (2.6")	400 (15.7")	Orange/Orange/Orange	12	50137-88
1.14 (0.045")	67 (2.6")	400 (15.7")	Red/Red/Red	12	50137-95