

## Cole-Parmer® Solvent-Resistant PVC 2-Stop Pump Tubing


Stopped tubing ensures a perfect fit every time. Stops hold tubing in pump head for optimal tension, resulting in reliable pumping and repeatable flow rates. It delivers accurate and interference-free analytical results. Use solvent-resistant PVC tubing with aromatic oils, solvents, and petroleum products. It exhibits similar chemical resistance characteristics to Viton® tubing, but at a lower cost, making it an excellent alternative. The phthalate-free and anti-leaching characteristics minimize the risk of interferences or false positives, ensuring accurate and reliable results. Bright yellow translucent tubing helps differentiate from standard PVC stop tubing.



### CERTIFICATION

USP Class VI compliant

### SOLVENT-RESISTANT PVC 2-STOP PUMP TUBING SIZE



### APPLICATIONS

- Perfect for general lab use, industrial applications like inks and oils, and use in peristaltic pumps
- Ideal for general-purpose, laboratory, and single-use applications

### FEATURES/BENEFITS

- Two tubing stops are color-coded for easy size identification
- Sterilize via autoclave or ethylene oxide
- Withstands a wide temperature range of -50 to 74 °C (-58 to 165 °F)
- Flexible tubing with a 61 Shore A durometer
- Yellow transparent tubing—perfect for visual confirmation of fluid flow
- Tubing does not contain SVHCs and is phthalate-free
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

**Cole-Parmer®**

[coleparmer.com](http://coleparmer.com)

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

## Specification and Ordering Table

Dimensions: mm (in.)			Color-Coded Stops	Tubes/Pack	Item Number
Tubing ID	Length Between Stops	Tubing Length			
0.19 (0.0075")	140 (5.5")	455 (17.9")	Orange/Red	12	<a href="#">50137-05</a>
0.25 (0.001")	140 (5.5")	455 (17.9")	Orange/Blue	12	<a href="#">50137-11</a>
0.38 (0.015")	140 (5.5")	455 (17.9")	Orange/Green	12	<a href="#">50137-15</a>
0.51 (0.02")	140 (5.5")	455 (17.9")	Orange/Yellow	12	<a href="#">50137-19</a>
0.64 (0.025")	140 (5.5")	455 (17.9")	Orange/White	12	<a href="#">50137-23</a>
0.76 (0.03")	140 (5.5")	455 (17.9")	Black/Black	12	<a href="#">50137-27</a>
0.89 (0.035")	140 (5.5")	455 (17.9")	Orange/Orange	12	<a href="#">50137-31</a>
1.02 (0.04")	140 (5.5")	455 (17.9")	White/White	12	<a href="#">50137-35</a>
1.14 (0.045")	140 (5.5")	455 (17.9")	Red/Red	12	<a href="#">50137-39</a>
1.3 (0.05")	140 (5.5")	455 (17.9")	Gray/Gray	12	<a href="#">50137-43</a>
1.52 (0.06")	140 (5.5")	455 (17.9")	Yellow/Blue	12	<a href="#">50137-48</a>
1.65 (0.065")	140 (5.5")	455 (17.9")	Blue/Blue	12	<a href="#">50137-52</a>
1.85 (0.073")	140 (5.5")	455 (17.9")	Green/Green	12	<a href="#">50137-56</a>
2.06 (0.08")	140 (5.5")	455 (17.9")	Purple/Purple	12	<a href="#">50137-59</a>
2.29 (0.09")	140 (5.5")	455 (17.9")	Purple/Black	12	<a href="#">50137-62</a>
2.54 (0.1")	140 (5.5")	455 (17.9")	Purple/Orange	12	<a href="#">50137-64</a>
2.79 (0.11")	140 (5.5")	455 (17.9")	Purple/White	12	<a href="#">50137-67</a>