

Tygon® 2375 Chemical-Resistant Transfer Tubing

Tygon® 2375 chemical transfer tubing delivers exceptional performance in environments where aggressive chemicals are present. Offering a unique combination of chemical resistance, clarity, and flexibility, this tubing is virtually unaffected by acids, bases, ketones, salts, and alcohols.

Plasticizer-free, non-DEHP construction eliminates the risk of fluid contamination while also preventing premature brittleness and cracking. A smooth inner surface enhances flow and reduces particulate buildup, while low sorption characteristics help maintain fluid purity and minimize cross-contamination.



Scan the QR code for more information on tubing.

APPLICATIONS

- Perfect for industrial cleaning, chemical analyzers, and ink dispensing
- Ideal for general-purpose, laboratory, and single-use applications

FEATURES/BENEFITS

- Plasticizer-free, non-DEHP construction
- Smooth inner surface improves flow and reduces particulate buildup
- Safer disposal—does not release harmful hydrogen chloride gases
- Wide temperature range of -75 to 54 °C (-103 to 130 °F)
- Flexible tubing with a 75 Shore A durometer
- Clear tubing—perfect for easily viewing your sample
- Excellent chemical resistance to concentrated bases, salts, and alcohol
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Specification and Ordering Table

Dimensions: in. (mm)			Max PSI at 73 °F (Bar at 23 °F)	Item Number	Reel Length (ft)
Tubing ID	Tubing OD	Wall			
1/16" (1.6)	3/16" (4.8)	1/16" (1.6)	65 (4.5)	48526-60	50
3/32" (2.4)	5/32" (4)	1/32" (0.8)	25 (1.7)	48526-61	50
1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	40 (2.8)	48526-62	50
5/32" (4)	7/32" (5.6)	1/32" (0.8)	20 (1.4)	48526-63	50
3/16" (4.8)	5/16" (8)	1/16" (1.6)	30 (2.1)	48526-64	50
1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	25 (1.7)	48526-65	50
5/16" (8)	7/16" (11)	1/16" (1.6)	20 (1.4)	48526-66	50
3/8" (9.5)	1/2" (12.7)	1/16" (1.6)	17 (1.2)	48526-67	50
3/8" (9.5)	5/8" (15.9)	1/8" (3.2)	25 (1.7)	48526-68	50
1/2" (12.7)	3/4" (19.1)	1/8" (3.2)	25 (1.7)	48526-69	50
5/8" (15.9)	7/8" (22.2)	1/8" (3.2)	20 (1.4)	48526-70	50
3/4" (19.1)	1" (25.4)	1/8" (3.2)	17 (1.2)	48526-71	50
1" (25.4)	1-3/8" (35)	3/16" (4.8)	19 (1.3)	48526-72	50