

## Versilon® ETFE Tubing

Versilon® ETFE tubing is engineered for applications requiring a combination of mechanical durability, chemical resistance, and environmental stability. Offering improved strength and impact resistance compared to many fluoropolymers, it is well-suited for use in demanding conditions where abrasion, stress, or repeated handling are concerns. Its resistance to radiation and weathering makes it a reliable choice for specialized environments, while its chemical compatibility supports use with a wide range of solvents and process fluids.



Scan the QR code for more information on tubing.

### APPLICATIONS

- Perfect for aerospace, automotive, and chemical processing
- Ideal for general-purpose, laboratory, and single-use applications

### FEATURES/BENEFITS

- High mechanical strength and impact resistance enhances durability
- Resistant to radiation, abrasion, and weathering for long-term reliability
- Sterilize via autoclave, ethylene oxide (EtO), or gamma irradiation
- Wide temperature range of -66 to 150 °C (-87 to 302 °F)
- Rigid tubing with a 72 Shore D durometer
- Excellent chemical resistance supports use with a wide range of fluids and solvents
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

## Cole-Parmer®

[coleparmer.com](http://coleparmer.com)

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

## Specification and Ordering Table

Dimensions: in. (mm)			Item Number	Reel Length (ft)
Tubing ID	Tubing OD	Wall		
1/64" (0.41)	1/16" (1.6)	1/50" (0.59)	<a href="#">48526-50</a>	50
1/50" (0.51)	1/16" (1.6)	1/50" (0.54)	<a href="#">48526-49</a>	50
1/16" (1.6)	1/8" (3.2)	1/32" (0.8)	<a href="#">48526-52</a>	50
3/32" (2.4)	1/8" (3.2)	1/64" (0.4)	<a href="#">48526-51</a>	50
1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	<a href="#">48526-54</a>	50
3/16" (4.8)	1/4" (6.4)	1/32" (0.8)	<a href="#">48526-53</a>	50
15/64" (5.9)	5/16" (8)	1/25" (1.02)	<a href="#">48526-55</a>	50
9/32" (7.1)	3/8" (9.5)	3/64" (1.2)	<a href="#">48526-56</a>	50
3/8" (9.5)	1/2" (12.7)	1/16" (1.6)	<a href="#">48526-57</a>	50