

# Cole-Parmer® Anti-static Chairs



**Class  
100**

## Cleanroom Certified with Ergonomic Comfort

Cole-Parmer Class 100-certified cleanroom chairs are upholstered in special conductive Polyurethane(PU) and Polypropylene(PP) to meet the stringent Cleanroom and ESD requirement. The Chair frame from the back to the base is electrically conductive to ensure static charges are dissipated through to the floor. These durable chairs offer total body support with advanced ergonomic features that reduce fatigue and improve productivity. Adjustable height with back tilt offers individual settings and supports 360° swivel. The chair components are shipped in sealed plastic to prevent contamination during transportation. Product packaging includes manual on unpacking and assembling in Cleanroom environment.

### Key Features:

- ◆ **ESD-protective construction (10<sup>6</sup>-10<sup>9</sup> ohms):** Helps prevent damage to sensitive equipment and circuitry
- ◆ **Easy seat height adjustments:** Promote circulation and relieves tension
- ◆ **Conductive high-comfort upholstery:** Provides stability, proper posture, and maximum comfort
- ◆ **Safety gas lift and nylon wheels with 5-star stainless steel base** - Increase chair stability and long wear resistance for adjustable options
- ◆ **Seat baseboard:** 3mm cold chrome plate

### Technical Specifications and Ordering Information:

Product SKU	Type	Dimensions (mm)	Seat Height (mm)	Surface Resistance	Grounding Resistance	Foot Ring
<b>Conductive Polyurethane (PU)</b>						
MK-15972-39	Stool	Seat Dia.: 310	Adjustable, 400-550	≤9.9*10 <sup>8</sup> Ω	≤9.9*10 <sup>8</sup> Ω	N
MK-15970-39	Stool	Seat Dia.: 330	Adjustable, 580-850	10 <sup>5</sup> -10 <sup>9</sup> Ω	≤10 <sup>9</sup> Ω	Y
MK-15972-38	Chair	Seat: 450x430 Back: 410x350	Adjustable, 400-550	1.0*10 <sup>5</sup> -9.9*10 <sup>8</sup> Ω	≤9.9*10 <sup>8</sup> Ω	N
MK-15970-38	Chair	Seat: 450x430 Back: 410x350	Adjustable, 580-850	1.0*10 <sup>5</sup> -9.9*10 <sup>8</sup> Ω	≤9.9*10 <sup>8</sup> Ω	Y
MK-15972-37	Chair	Seat: 450x430 Back: 410x350	Adjustable, 580-850	10 <sup>7</sup> -10 <sup>9</sup> Ω	≤10 <sup>8</sup> Ω	N
<b>Conductive Polypropylene (PP)</b>						
MK-15972-36	Chair	Seat: 450x430 Back: 410x350	Non-adjustable	≤1*10 <sup>10</sup> Ω	≤1*10 <sup>9</sup> Ω	N
MK-15972-40	Stool	Seat Dia.:310	Non-adjustable	≤1*10 <sup>10</sup> Ω	≤1*10 <sup>9</sup> Ω	N